Part Number: 0887388000
Status: Active
Overview: USB Products and Solutions
Description: Universal Serial Bus (USB) I/O Cable Assembly: A-to-Pigtail Sub-Channel, 0.81m Length



Series image - Reference only

Documents:
3D Model
Drawing (PDF)
RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	68594
Assembly Configuration	Single Ended Connector
Comments	Sub-Channel, Sub-Channel
Connector to Connector	USB Type A-to-Pigtail
Overview	USB Products and Solutions
Product Name	USB
UPC	800753942820
Physical	
Cable Length	0.81m
Circuits (Loaded)	4
Gender	Male
Lock to Mating Part	Yes
Net Weight	22.500/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	2.00mm, 2.50mm
Single Ended	Yes
Wire Insulation Diameter	N/A
Wire Size AWG	N/A
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	1.0A
Shielded	No
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-88738-001-001

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
68594 Series

Mates With
Universal Serial Bus (USB) Type A Receptacle 67329 , 67230 , 89485

Downloaded from Arrow.com.