NON-LIGHTED DISPLAY



PWB Mount



Panel Mount

FEATURES

- Printed circuit board or snap-in panel mounting
- Bezels and mounting clips, and legended lenses can be furnished installed or ordered separately
- UL recognized, CSA certified.

Example: MML31KK2AAK
Power duty pushbutton switch housing (black); bezel (black) and mounting clips; solder terminals; 1 pole, momentary action; black plunger.

Example: MML31KK2AAKLR
As above, except furnished with red lens.

MML31 ORDER GUIDE

Catalog listing codes for switch, less assembled display options

MML31K	K	2	AA
Housing Type (Rectangular)	**Mounting**	**Terminals**	**Circuitry/Action** (Each pole is single-throw, normally open)
MML31K Black housing, non-lighted	**A** No bezel (PWB mounting) **K** Black bezel, mtg. clip/long sides	**3** Printed wiring board **2** Solder/Quick-connect	**AA** 1 pole, mom. action **AB** 1 pole, alt. action **AC** 2 poles, mom. action **AD** 2 poles, alt. action

Downloaded from Arrow.com.

Electrical Data	page 69
Bezels	page 84
Strip and matrix mounting	page 83
Mounting dimensions	pages 97/98
PWB pin locations	page 97

Order display options assembled to switch by adding codes below

K

Plunger
K Black

LR

Lens	
LR	Red
LY	Yellow
LG	Green
LW	White
LK	Black

Leave this space blank, if legend not desired

Legend
20 With Legend
Use Legend Order Sheet FO-74024 to cover each catalog listing (see page 81).

Downloaded from Arrow.com.