DSUB SV MA SSDP ANG36-254 25P AU3

Spotted an error? | Print page | Back

Image is for illustration purposes only. Please refer to product description.

Alternatives

Accessories

Combinables

Login to MyHARTING for pricing and stock check

Quantity: 100

Shopping cart

Email inquiry

Catalogue
HARTING Device Connectivity - Page 252

Browse

Download

- Features
- Connection data
- Dimensions and weight
- Supplementals

Part number:	09 66 362 7815
Description:	DSUB SV MA SSDP ANG36-254 25P AU3

Features

Application:	Board Connector
Contact Pitch:	2.54 mm
Gender:	Turned Male Contact
Mating Hardware:	Flange Thread M3
No. of contacts:	25
Performance level:	PL3
RoHS conformity:	Yes
Termination Type:	Solder
Type:	Right Angled Low Profile
Locking type:	With Grounding Board Lock

Top

Connection data

Current:	7 A @ 20°C

Top

Dimensions and weight

Net Weight:	16.6 g

Top

Supplementals

Series:	D-Sub Standard
Limiting temperature, min.:	-55 °C
Limiting temperature, max.:	125 °C

Top

Downloads

Title	Download
CAD data 3D	IGES
CAD data 3D	STEP
CAD data 3D	VRML
HARTING Device Connectivity - Page 252	PDF

Alternatives

Image	Part number	Net Weight	Performance level	Tech. info	Quantity
	09 66 362 6815	12.2 g	PL2		1 Shopping cart

Accessories

Image	Part number	Description	Tech. info	Quantity
	09 67 025 0611	D-Sub Dust cap male connector 25-pole		1 Shopping cart
	09 67 025 0612	D SUB FE 25 pole antist. pla. dust cap		1 Shopping cart
	09 67 025 0613	D SUB MA 25 pole Plastic Dust Cap UL 94		1 Shopping cart
	09 67 025 0614	D SUB MA 25 pole metallized plastic dust		1 Shopping cart
	09 67 025 0615	DSUB MA 25pol.metal.plastic cap w.chain		1 Shopping cart

Combinables

Image	Part number	Description	Tech. info	Quantity
	09 67 025 4701	D-Sub crimp 25-pole female assembly		1 Shopping cart
	09 67 225 4704	D SUB FE STAMPED SOLDER CUP 25 PL3		1 Shopping cart
	09 67 025 4704	DSUB SV FE TSDC 25P AU3		1 Shopping cart
	09 66 318 7500	D-SUB 25F-IDC		1 Shopping cart

Recently viewed - Delete

DIN-Power 2F 024 Übergangselement U

Show product details

DIN-Signal harbus64 insert block shroud

Show product details

Cable Sealing thermoplastic PG16

Show product details

Cable Sealing thermop PG21 20,5-17mm bla

Show product details

Acces. Cable Clamp PG 11 Metal

Show product details

Han 3A Thermoplastic Locking Lever grey

Show product details

Han 10/16/24B Thermoplastic Lock. Lever

Show product details

Grommet 3-4mm KDT/Z3 for Split Hood

Show product details

Grommet 6-7mm KDT/Z6 for Split Hood

Show product details

Han Easy-Lock X-6B-Single lever

Show product details

Recently searched

No searches have been done yet.

Downloaded from Arrow.com.