Part Number : 02096123
Product Description : 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Gold (Au) Plated Brass Contact, 22-18 AWG, Bag
Series Number : 1380
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : 1380-(550)L
Packaging Alternative : 02096122 (Reel)



Documents and Resources

Drawings

002096123_sd.pdf

PK-1190-003-001.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-02-09-001.pdf

11890000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	1380
Description	2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Gold (Au) Plated Brass Contact, 22-18 AWG, Bag
Application	Wire-to-Wire
Product Name	Standard .093"
UPC	800754230384

Physical

Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.414/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.254µm

Downloaded from Arrow.com.

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size (AWG)	18, 20, 22
Wire Size mm^2	N/A

Application Tooling

Global

Description	Part Number
Insertion Tool for Standard .093" Pin and Socket Terminals	11020003
Extraction Tool for Standard .093" Pin and Socket Terminals	11030006
Extractor Tool for .093 and HCS-125 Product Series	638240200
Hand Crimp Tool for Standard .093" Pin and Socket Crimp Terminals, 18 AWG	638280900
Hand Crimp Tool for Standard .093" Pin and Socket Crimp Terminals, 20 AWG	638281700

Downloaded from Arrow.com.