Pushing Performance
Since 1945

# Han 16EMC/B-HSE-M32 (HT)




Image is for illustration purposes only. Please refer to product description.

| | |
|---|---|
| Part number | 19 62 816 0527 |
| Specification | Han 16EMC/B-HSE-M32 (HT) |
| HARTING eCatalogue | https://harting.com/19628160527 |

## Identification

| | |
|---|---|
| Category | Hoods / Housings |
| Series of hoods/housings | Han® EMC/B<br>Han® High Temp |
| Type of hood/housing | Hood |
| Type | High construction |

## Version

| | |
|---|---|
| Size | 16 B |
| Version | Side entry |
| Number of cable entries | 1 |
| Cable entry | 1x M32 |
| Locking type | Double locking lever |
| Field of application | Hoods/Housings for higher EMC requirements |

## Technical characteristics

| | |
|---|---|
| Limiting temperature | -40 ... +125 °C<br>-40 ... +200 °C With Han® High Temp components |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Mating cycles | ≥500 |
| Degree of protection acc. to IEC 60529 | IP65<br>IP66 |
| Type rating acc. to UL 50 / UL 50E | 4<br>12 |


HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

## Material properties

| | |
|---|---|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Uncoated |
| Colour (hood/housing) | Unpainted |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| PFAS | No |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Nickel |

## Specifications and approvals

| | |
|---|---|
| UL / CSA | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE<br>UKCA<br>DNV GL |

## Commercial data

| | |
|---|---|
| Packaging size | 1 |
| Net weight | 160 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140132931 |
| eCl@ss | 27440202 Shell for industrial connectors |
| ETIM | EC000437 |
| UNSPSC 24.0 | 39121466 |


HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.