Part Number : 393710003
Product Description : 7.50mm Beau Eurostyle Pluggable Terminal Block, 180° Wire Entry, 3 Circuits
Series Number : 39371
Status : Active
Product Category : Terminal Blocks and Barrier Strip
Engineering Part Number : MX-CIF03003-0N



Documents and Resources

Drawings

393710003_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39371
Description	7.50mm Beau Eurostyle Pluggable Terminal Block, 180° Wire Entry, 3 Circuits
Application	Wire-to-Board
Component Type	Plug
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822348040179

Agency

UL	E48521

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black

Downloaded from Arrow.com.

Entry Angle	180° Angle
Flammability	94V-0
Lock to Mating Part	No
Number of Rows	1
Orientation	N/A
Panel Mount	No
PCB Retention	N/A
Pitch - Mating Interface	7.50mm
Pitch - Termination Interface	7.50mm
Polarized to Mating Part	Yes
Stackable	Yes
Temperature Range - Operating	110°C
Wire Size (AWG)	12, 14, 16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm^2	0.05-2.50

Mates With / Use With

Mates with Part(s)

Description	Part Number
7.50mm Beau Eurostyle Vertical PCB Headers	39372
7.50mm Beau Eurostyle Horizontal PCB Headers	39373

Downloaded from Arrow.com.