



REV. 3
DCO 63333

COIL: @ 25°C

RESISTANCE	390 OHMS ±10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	14.0 VDC @ 25°C
MUST RELEASE	1.4 VDC @ 25°C

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 15 g's
SHOCK 100 g's 6 MS. DURATION
TEMPERATURE -65 °C TO +125 °C

NOTES: TERMINALS ARE GOLD PLATED
OPERATE & RELEASE 5 MS MAX.
BOUNCE 5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 2 AMP 28 VDC RESISTIVE

DR. R.B. 11/29/90 CK. TLG 10-24-00

CII Technologies
advanced control electronic solutions

CUST. CII STD
CUST. NO. _____ REV. _____

"SRBW" RELAY

SRBW-4C-24G

SUPERSEDED
NOT the LATEST REVISION

Downloaded from Arrow.com.