TRACO POWER

Inductor

TCK-070

Order Code	TCK-070
Inductance	10 µH ±20% (at 1 kHz / 250 mV)
Impedance (DCR)	40 mΩ max.
Rated Current	2.6 A max.
Operating Temperature	-40°C to +125°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-070



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	7.0 ±0.5
B	7.8 ±0.5
C	5.0 ±0.7
D	2.1 typ.
E	7.5
F	3
G	2

All specifications valid at +25°C, unless otherwise stated.

© Copyright 2026 Traco Electronic AG Specifications can be changed without notice.

Downloaded from Arrow.com.