TRUNK CABLE P/N	OVERALL LENGTH, L (m)	CABLE TYPE	FIBER TYPE	CONNECTOR/ CABLE COLOR	INSERTION LOSS	RETURN LOSS
1062250100	1.0 +0.2 / -0	SINGLE JACKET	MM 50/125 µm OM3 BIF	AQUA / AQUA	0.35 dB @ 850 nm	---
1062250101	3.0 +0.2 / -0					
1062250102	5.0 +0.2 / -0					
1062250103	10.0 +0.2 / -0					
1062250104	15.0 +0.3 / -0					
1062250105	25.0 +0.5 / -0	RUGGEDIZED CENTRAL TUBE				
1062250106	50.0 +1.0 / -0					
1062250107	100.0 +2.0 / -0					
1062250110	1.0 +0.2 / -0	SINGLE JACKET	MM 50/125 µm OM4 BIF			
1062250111	3.0 +0.2 / -0					
1062250112	5.0 +0.2 / -0					
1062250113	10.0 +0.2 / -0					
1062250114	15.0 +0.3 / -0					
1062250115	25.0 +0.5 / -0	RUGGEDIZED CENTRAL TUBE				
1062250116	50.0 +1.0 / -0					
1062250117	100.0 +2.0 / -0					
1062250120	1.0 +0.2 / -0	SINGLE JACKET	SM 9/125 µm OS2 ITU-T G.657.A1 BIF	YELLOW / YELLOW	0.35 dB @ 1550 nm	- 50 dB @ 1550 nm
1062250121	3.0 +0.2 / -0					
1062250122	5.0 +0.2 / -0					
1062250123	10.0 +0.2 / -0					
1062250124	15.0 +0.3 / -0					
1062250125	25.0 +0.5 / -0	RUGGEDIZED CENTRAL TUBE				
1062250126	50.0 +1.0 / -0					
1062250127	100.0 +2.0 / -0					

CONNECTIONS	
FROM	TO
P1-1 THRU P1-12	P2-12 THRU P2-1



SINGLE JACKET



RUGGEDIZED CENTRAL TUBE

NOTES:

1. ENDCAPS ARE NOT SHOWN BUT INLCUDED.
2. LABEL IS PRINTED WITH MOLEX P/N AND SERIAL NUMBER.
3. FOR DETAILED PRODUCT SPECIFICATION SEE DOCUMENT 1062250000 ES.
4. CABLE CONSTRUCTION:
   - L < 25 meters - SINGLE JACKET CABLE
   - L ≥ 25 meters - RUGGEDIZED CENTRAL TUBE CABLE
5. INSERTION LOSS TEST DATA IS PROVIDED WITH EACH SHIPMENT.
6. PACKAGING:
   - L < 50 meters - INDIVIDUALLY COILED AND BAGGED
   - L ≥ 50 meters - SHIPPED ON SPOOLS



VIEW A
SCALE 5:1



VIEW B
SCALE 5:1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
mm	1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL	± °
4 PLACES	±
3 PLACES	±
2 PLACES	±
1 PLACE	±
0 PLACES	±

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 688262
DRWN: JHUANG18 2021/12/08
CHK'D: IGUMIN 2021/12/10
APPR: IGUMIN 2021/12/10

INITIAL REVISION:
DRWN: MAGHAYERE01 2018/04/30
APPR: IGUMIN 2018/05/16

THIRD ANGLE PROJECTION | DRAWING: D-SIZE | SERIES: 106225

molex

MPO(F) - MPO(F) TRUNK CABLE, 12 FIBER, PLENUM

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
1062250100	PSD	000	B

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE TABLE		1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2021/12/10 01:38:45

Downloaded from Arrow.com.