Product Details for 207595 -6

No Image Available

207595 -6

Active

ARINC 404 Connectors

Not ELV or RoHS Compliant

Product Highlights:

- Sealed
- Seal Type = Environmental
- Shell Size = 2 Inserts
- Shell Configuration = Receptacle
- Contact Arrangement (Module A) = 106

View all Features

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- RECEPTACLE CONN. INSTALLATION (WITH CENTER FEMALE JA... (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

List all Documents

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Sealed = Yes
- Shell Size = 2 Inserts
- Shell Finish = Electroless Nickel
- Thread Size = 10 -24 Double Lead Thread, Self - Locking
- Comment = Coaxial contacts must be ordered separately

Mechanical Attachment:

- Keying = 04
- Hardware Type = Center Female Jackscrew

Electrical Characteristics:

- Shell Configuration = Receptacle
- Signal Contacts = With
- Shell Mounting Modification = 50
- Custom Order Code = 250

Termination Related Features:

- Seal Type = Environmental

Contact Related Features:

- Contact Type (Module A) = Socket
- Contact Type (Module B) = Pin

Configuration Related Features:

- Contact Arrangement (Module A) = 106
- Contact Arrangement (Module B) = 26

Industry Standards:

- Government/Industry Qualification = No
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

Other:

- Brand = AMP

© 2006 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.