Watertight - Thick Wall Diecast Aluminum *R190-R191 Series*

aluCASE







Key Features:

- Modern, high quality instrument enclosure.
- Made of diecast aluminum material (GD Al Si 12/DIN 1725).
- Includes captive stainless steel lid screws.
- Internal mounting channels can be accessed after lid is closed.
- 1.7mm recess is integrated in lid for membrane keypads and front panels.
- Comes with preformed TPE gasket installed.
- Clip-on screw covers hide mounting and lid screws.
  - Screw covers are made of RAL 7040 grey PMO plastic.
- Degree of protection: NEMA 4X, IP67.
- CSA and UL listed to Type 4.
- Finished in textured RAL 7040 gray polyester powder coat, RAL 7040 grey.
  - Can be supplied unpainted on special order.

Features (click to enlarge)



Enclosure can be installed after closing lid.



Includes optional-use lid captivation straps.

Downloaded from Arrow.com.



Snap-in design covers hide both lid screws and installation holes.



All holes are outside of gasket seal.

Part Number	Length (mm)	Width (mm)	Depth With Lid (mm)
R191-052-000	50	75	33
R191-054-000	50	100	33
R191-070-000	70	100	50
R191-090-000	90	120	60
R191-072-000	70	140	50
R190-110-000	110	140	60
R191-092-000	90	160	60
R190-130-000	130	160	70
R191-074-000	70	180	50
R190-150-000	150	180	60
R191-150-000	150	180	90
R190-112-000	110	200	60
R190-170-000	170	200	60
R191-170-000	170	200	90
R190-132-000	130	220	70
R191-200-100	200	230	120
R191-094-000	90	250	60
R190-152-000	150	260	60
R191-152-000	150	260	90
R190-172-000	170	280	60
R191-172-000	170	280	90
R191-202-100	200	330	120

Tags: **Rolec**, **diecast**, **aluminum**, **thick wall**, **NEMA**, **screw cover**, **alucase**

Data subject to change without notice.

© 2026. Hammond Manufacturing Ltd. All rights reserved.

Downloaded from Arrow.com.