



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2016
© COPYRIGHT 2016 BY TE CONNECTIVITY ALL RIGHTS RESERVED.


| REVISIONS | | | | | |
|---|---|---|---|---|---|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | NC | NEW RELEASE PER E.O. P18478 | 29JAN2004 | - | RDR |
| | B | REVISED PER PCN-24-222744 | 18SEP2024 | GB | CB |
| | | | | | |
| | | | | | |




| TE INTERNAL PN | DEUTSCH PN |
|---|---|
| DT06-3S-CE14 | DT06-3S-CE14 |

| CONTACT SIZE | MIN. INSUL O.D. | MAX. INSUL O.D. | ⚠1 WIRE RANGE [$mm^2$] REF ONLY |
|---|---|---|---|
| 16 | .053 [1.35] | .120 [3.05] | 14-20 AWG [2.5-0.5] |

5. MATERIAL: HOUSING: PA66 GF15 (BLACK)
CAP: PA66 GF15 (BLACK)
FRONT SEAL: VMQ (RED-ORANGE)
GROMMET: VMQ (BURNT RED)

4. THIS CONNECTOR CAN PASS THRU A ONE INCH [25.4 mm] HOLE.

3. THIS PLUG MATES WITH DT04-3P-XXXX RECEPTACLE
(XXXX = ALL MODIFICATIONS) CONSULT FACTORY FOR MODIFICATION

2. WEDGE LOCK W3S-P012 SOLD SEPERATLY.

⚠1 FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATON CHARACTERSTICS SEE ENVELOPE DRAWING 0425-015-0000 AND 0425-017-0000.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: in [mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±.025 [0.64]
4 PLC ±
ANGLES ±1°

MATERIAL 3

FINISH

DWN T. YOHANNES 26JAN2004
CHK R. MILLIGAN 29JAN2004
APVD S. BEARD 29JAN2004
PRODUCT SPEC 108-151009
APPLICATION SPEC 114-151009
WEIGHT 7.00g

TE Connectivity

NAME 3 WAY PLUG WITH REDUCED DIAM. SEAL -CE14 MOD. DT SERIES

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A3 | 4AFU8 | C-DT06-3S-CE14 | |

CUSTOMER DRAWING | SCALE 2.5:1 | SHEET 1 OF 1 | REV B

1470-19 (3/13)

Downloaded from Arrow.com.