

D-440-0108 Product Details

[Share](#) [Print](#) [Email](#)


✓ Active

MiniSeal Splices

D-440-0108

D-440-0108

TE Internal Number: 650120-000

Product Highlights [View All](#)

- Splice Type = Butt (in-line)
- Crimp Barrel Size = 779 - 2680 CMA
- Side 1 Max. # of Wires = 2 or 3
- Side 2 Max. # of Wires = 2 or 3
- RoHS compliant, ELV compliant

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#)
[Features](#)
[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Splice Type [?]	Butt (in-line)
Color Code	Blue Stripe in Crimp

Termination Features

Crimp Barrel Size (CMA [mm ²]) [?]	779 - 2680 [0.39 - 1.34]
Connection Type	Stub Splice
Crimp Barrel Plating	Nickel
Wire/Cable Size (AWG)	20

Body Features

Insulation Material	Polytetrafluoroethylene
---------------------	-------------------------

Housing Features

Side 1 Max. # of Wires	2 or 3
Side 2 Max. # of Wires	2 or 3
Side 1 Sealing Insert I.D. (mm [in])	1.60 [0.063]
Side 2 Sealing Insert I.D. (mm [in])	1.60 [0.063]

Industry Standards

Government/Industry Qualification	No
MIL Specification [MIL-S-81824] [?]	No
RoHS/ELV Compliance [?]	RoHS compliant, ELV compliant
Lead Free Solder Processes [?]	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Environmental

Operating Temperature (Max.) (°C)	200
-----------------------------------	-----

Operation/Application

Application Type	Wire Splice
------------------	-------------

Other

Brand	Raychem
-------	---------

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

