

# Product data sheet

Specifications



## APC IT Power Distribution Module 3 Pole 5 Wire 20A 240V IEC309 200cm

PDM3520IEC309-200

### Overview

|              |  |
|--------------|--|
| Presentation | Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time. |
|--------------|--|

|           |                              |
|-----------|------------------------------|
| Lead time | Usually Ships within 3 Weeks |
|-----------|------------------------------|

### Main

|                       |                    |
|-----------------------|--------------------|
| Main Input Voltage    | 230 V              |
| Main Output Voltage   | 240 V              |
| Input Connection Type | IEC 60309          |
| Provided equipment    | Installation guide |

### Physical

|            |         |
|------------|---------|
| Colour     | Grey    |
| Height     | 12.7 cm |
| Width      | 44.4 cm |
| Depth      | 40.6 cm |
| Net weight | 3.73 kg |

### Input

|                     |             |
|---------------------|-------------|
| Network frequency   | 60 Hz       |
| Permissible voltage | 200...240 V |
| Max line current    | 20 A        |

### Output

|                                |           |
|--------------------------------|-----------|
| Max current draw               | 20 A      |
| Number of power socket outlets | 1 IEC 309 |

### Conformance

|                        |           |
|------------------------|-----------|
| Product certifications | UL listed |
|------------------------|-----------|

### Packing Units

|                        |    |
|------------------------|----|
| Unit Type of Package 1 | Db |
|------------------------|----|

|                              |         |
|------------------------------|---------|
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 12.7 cm |
| Package 1 Width              | 40.6 cm |
| Package 1 Length             | 44.4 cm |
| Package 1 Weight             | 4.27 kg |

Offer Sustainability

|                            |   |
|----------------------------|---|
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Under investigation                           |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | <a href="#">End of Life Information</a>       |
| Take-back                  | Take-back program available                   |

Contractual warranty

|          |                          |
|----------|--------------------------|
| Warranty | 1 year repair or replace |
|----------|--------------------------|

Recommended replacement(s)