



# HIRSCHMANN

A BELDEN BRAND

## Product information MAS 7100 S grau/grey

Industrial Connecting Solutions: Circular Connectors: Audio/Video Connectors: DIN EN 60 130-09 Connectors (MAS/MAK series): with locking screw: Straight plugs: MAS 7100 S grau/grey


<https://catalog.beldensolutions.com:443/link/57078-24228-256281-256282-24384-24391-24393-34574/en/conf/ui/state>

|                                   |                                       |
|-----------------------------------|---------------------------------------|
| Name                              | MAS 7100 S grau/grey                  |
|                                   |                                       |
|                                   | plug with locking screw; solder joint |
| Delivery informations             |                                       |
| Availability                      | available                             |
| Product description               |                                       |
| Type                              | MAS 7100 S grau/grey                  |
| Order No.                         | 930 688-517                           |
| Type of contact                   | male                                  |
| Description                       | plug with locking screw; solder joint |
| Housing Color                     | grey                                  |
| Number of contacts                | 7                                     |
| Conductor size                    | $\leq 0.34 \text{ mm}^2$              |
| Technical data                    |                                       |
| LF output "Phone"                 | EN 60 130-09                          |
| Pole arrangement DIN              | DIN 45 329                            |
| Rated current                     | 4 A                                   |
| Rated voltage                     | AC/DC 34 V                            |
| Cable diameter                    | 5.5 mm                                |
| Type of termination               | solder                                |
| Material                          |                                       |
| Contact material                  | brass                                 |
| Contact surface material          | tin plated                            |
| Contact bearer material           | PA 66/UL standard 94V-2               |
| Housing material                  | PE                                    |
| Environmental conditions          |                                       |
| Protection class (IEC 60529)      | IP 30                                 |
| Temperature range                 | -20 °C to +60 °C                      |
| Scope of delivery and accessories |                                       |
| Packaging                         | retail package, polyethylene bag      |

Industrial Connecting Solutions: Circular Connectors: Audio/Video Connectors: DIN EN 60 130-09 Connectors (MAS/MAK series): with locking screw: Straight plugs: MAS 7100 S grau/grey  
<https://catalog.beldensolutions.com:443/link/57078-24228-256281-256282-24384-24391-24393-34574/en/conf/uistate>

Picture

Drawing



**Belden Deutschland GmbH**  
Im Gewerbepark 2  
58579 Schalksmühle  
Germany  
Phone: +49 7127/14-1806  
E-Mail: [icos-sales@belden.com](mailto:icos-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.