Pushing Performance
Since 1945

# UIC558-HBM/CM-22PIN

Image is for illustration purposes only. Please refer to product description.

| | |
|---|---|
| Part number | 09 58 001 0303 |
| Specification | UIC558-HBM/CM-22PIN |
| HARTING eCatalogue | https://b2b.harting.com/09580010303 |

## Identification

| | |
|---|---|
| Category | Hoods/Housings |
| Series | HARTING UIC |
| Identification | 558 |
| Type of hood/housing | Bulkhead mounted housing |
| Description of hood/housing | With metal cover |

## Version

| | |
|---|---|
| Number of contacts | 22 |
| Field of application | Hoods/housings for harsh outdoor environments |

## Technical characteristics

| | |
|---|---|
| Limiting temperature | -50 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP69 / IPX9K acc. to ISO 20653 mated condition |

## Material properties

| | |
|---|---|
| Material (hood/housing) | Aluminium die-cast<br>Corrosion resistant |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 7035 (light grey) |
| Material (seal) | Silicone |
| Material (locking) | Stainless steel |


HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

## Specifications and approvals

| | |
|---|---|
| Specifications | UIC 50558 |
| | IRS 50558 |
| | IEC 61373 Category 2 |
| | IEC 60529 |

## Commercial data

| | |
|---|---|
| Packaging size | 1 |
| Net weight | 582.73 g |
| Country of origin | India |
| European customs tariff number | 85389099 |
| GTIN | 5713140183957 |
| ETIM | EC000437 |
| eCl@ss | 27440202 Shell for industrial connectors |


HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.