


 Share **Print** **Email**



TE Internal Number: 1-2007394-5

Active

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- SFP+ Product Line
- Cage Assembly with Integrated Connector
- SFP+ Enhanced EMI Application
- Connector Style = Receptacle
- Cage Type = Stacked

[View all Features](#)

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

[+] Feedback

Product Drawings:

- [CAGE AND PT CONNECTOR ASSEMBLY, WITH EMI SPRINGS, PR... \(PDF, English\)](#)

- None Available

- [SFP+ Stacked Connector and Cage Assemblies](#) (PDF, English)

- Stacked Small Form-Factor Pluggable (SFP+) Connector... (PDF, English)

- None Available

- None Available

- Tooling

[List all Documents](#)

- Product Line = SFP+
- Product Type = Cage Assembly with Integrated Connector

- PCB Mount = Single Sided

- Data Signal Rate (Gb/s) = Up to 16

- Termination Method to PC Board = Through Hole - Press Fit

- Tail Length (mm [in]) = 3 [0.118]
- PCB Thickness, Recommended (mm [in]) = 1.50 [0.059]
- Length (X-Axis) (mm [in]) = 63.50 [2.500]
- Width (Z-Axis) (mm [in]) = 57.41 [2.260]
- Profile Height (Y-Axis) (mm [in]) = 25.50 [1.0039]

- Integrated Light Pipes = Yes

- **Contact Plating, Mating Area, Material** = Gold or Gold Flash over Palladium Nickel
- **Contact Base Material** = Copper Alloy

- Connector Style = Receptacle
- **Cage Type** = Stacked
- Housing Material = Liquid Crystal Polymer (LCP)
- Housing Color = Black
- Cage Material = Nickel Silver

- Port Configuration = 2x4
- Lightpipe = With
- Lightpipe Configuration = All Four
- EMI Containment = External Springs

- **RoHS/ELV Compliance** = RoHS compliant, ELV compliant
- **Lead Free Solder Processes** = Not relevant for lead free processes
- **RoHS/ELV Compliance History** = Always was RoHS compliant
- **UL Flammability Rating** = UL 94V-0

- Applies To = Printed Circuit Board

- **Application** = SFP+ Enhanced EMI

- Packaging Method = Box/Cartron

- Brand = TE Connectivity

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)