Part Number : 638274900
Product Description : Hand Crimp Tool for Mega-Fit Crimp Terminals, mm^2 Wires
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents and Resources

Tooling Specifications

ATS-6382749HM-001.pdf

TM-638000029-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for Mega-Fit Crimp Terminals, mm^2 Wires
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Mega-Fit
Tool Type	Hand Crimp Tool
UPC	889056024174
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Downloaded from Arrow.com.

Applicable Parts

Description	Part Number
Mega-Fit Crimp Terminal, Female, Tin (Sn) Plating, 16-14 AWG, Reel	768230321
Mega-Fit Crimp Terminal, Female, Tin (Sn) Plating, 12 AWG, Reel	768230322
Mega-Fit Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 16-14 AWG, Reel	1720630311
Mega-Fit Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 12 AWG, Reel	1720630312
Mega-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 16-14 AWG, Reel	1720631311
Mega-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 12 AWG, Reel	1720631312

Downloaded from Arrow.com.