

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Profile, for screwing or riveting, 1000 mm long, for accommodating UC und US materials, height: 15 mm

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	25 pc
GTIN	 4 046356 614887
GTIN	4046356614887
Custom tariff number	39162000
Country of origin	Germany

Technical data

Dimensions

Length (b)	15 mm
Width (a)	1000 mm
Hole spacing	49.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Color	gray
Components	Silicone-free

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366

Technical data

General

Material	PVC
Mounting type	screw, rivet

Environmental Product Compliance

REACH SVHC	DOTe 15571-58-1
------------	-----------------

Classifications

eCl@ss

eCl@ss 10.0.1	27144075
eCl@ss 11.0	27281105
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 9.0	27144075

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 6.0	EC002248
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 19.0	39131504

Accessories

Accessories

Cover

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366

Accessories

Cover - CARRIER-EMP (1000X15) COVER - 0829520



Cover, transparent, unlabeled, lettering field size: 1000 x 15 mm


Device marking

Snap-in markers - UC-EMP (17X15) - 0825421



Snap-in markers, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 17 x 15 mm, Number of individual labels: 8

Snap-in markers - UC-EMP (17X15) SR - 0825423



Snap-in markers, Sheet, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 17 x 15 mm, Number of individual labels: 8

Snap-in markers - UC-EMP (17X15) YE - 0825422



Snap-in markers, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 17 x 15 mm, Number of individual labels: 8

Snap-in markers - UC-EMP (27X15) - 0825439



Snap-in markers, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 8

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366

Accessories

Snap-in markers - UC-EMP (27X15) SR - 0825441



Snap-in markers, Sheet, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 8

Snap-in markers - UC-EMP (27X15) YE - 0825440



Snap-in markers, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 8

Snap-in markers - UC-EMP (49X15) - 0825457




Snap-in markers, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 49 x 15 mm, Number of individual labels: 4

Snap-in markers - UC-EMP (49X15) RD - 0829498



Snap-in markers, Sheet, red, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 49 x 15 mm, Number of individual labels: 4

Snap-in markers - UC-EMP (49X15) SR - 0825459



Snap-in markers, Sheet, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 49 x 15 mm, Number of individual labels: 4

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366

Accessories

Snap-in markers - UC-EMP (49X15) YE - 0825458



Snap-in markers, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 49 x 15 mm, Number of individual labels: 4

Snap-in markers - UC-EMP (60X15) - 0822259



Snap-in markers, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 60 x 15 mm, Number of individual labels: 4

Snap-in markers - UC-EMP (60X15) SR - 0827647



Snap-in markers, Sheet, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID COLOR, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 60 x 15 mm, Number of individual labels: 4

Snap-in markers - UC-EMP (60X15) YE - 0825330



Snap-in markers, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 60 x 15 mm, Number of individual labels: 4

Snap-in markers - US-EMP (100X15) - 0829521



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 100 x 15 mm, Number of individual labels: 9

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366

Accessories

Snap-in markers - US-EMP (100X15) SR - 0829523



Snap-in markers, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 100 x 15 mm, Number of individual labels: 9

Snap-in markers - US-EMP (100X15) YE - 0829522



Snap-in markers, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 100 x 15 mm, Number of individual labels: 9

Snap-in markers - US-EMP (17X15) - 0828774



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 17 x 15 mm, Number of individual labels: 54

Snap-in markers - US-EMP (17X15) SR - 0828843



Snap-in markers, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 17 x 15 mm, Number of individual labels: 54

Snap-in markers - US-EMP (17X15) YE - 0828842



Snap-in markers, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 17 x 15 mm, Number of individual labels: 54

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366

Accessories

Snap-in markers - US-EMP (27X15) - 0828777



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 27

Snap-in markers - US-EMP (27X15) SR - 0828849



Snap-in markers, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 27

Snap-in markers - US-EMP (27X15) YE - 0828848

Snap-in markers, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 27

Snap-in markers - US-EMP (35X15) - 0830295



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 35 x 15 mm, Number of individual labels: 24

Snap-in markers - US-EMP (35X15) RD - 0830309



Snap-in markers, Card, red, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 35 x 15 mm, Number of individual labels: 24

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366

Accessories

Snap-in markers - US-EMP (35X15) SR - 0830308



Snap-in markers, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 35 x 15 mm, Number of individual labels: 24

Snap-in markers - US-EMP (35X15) YE - 0830307



Snap-in markers, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 35 x 15 mm, Number of individual labels: 24

Snap-in markers - US-EMP (49X15) - 0828780



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 49 x 15 mm, Number of individual labels: 18

Snap-in markers - US-EMP (49X15) SR - 0828855



Snap-in markers, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 49 x 15 mm, Number of individual labels: 18

Snap-in markers - US-EMP (49X15) YE - 0828854



Snap-in markers, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 49 x 15 mm, Number of individual labels: 18

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366


Accessories

Snap-in markers - US-EMP (52,5X15) - 0830296



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 52.5 x 15 mm, Number of individual labels: 16

Snap-in markers - US-EMP (52,5X15) RD - 0830312



Snap-in markers, Card, red, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 52.5 x 15 mm, Number of individual labels: 16

Snap-in markers - US-EMP (52,5X15) SR - 0830311



Snap-in markers, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 52.5 x 15 mm, Number of individual labels: 16

Snap-in markers - US-EMP (52,5X15) YE - 0830310



Snap-in markers, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 52.5 x 15 mm, Number of individual labels: 16

Snap-in markers - US-EMP (60X15) - 0828781



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 60 x 15 mm, Number of individual labels: 9

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366

Accessories

Snap-in markers - US-EMP (60X15) SR - 0828857



Snap-in markers, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 60 x 15 mm, Number of individual labels: 9

Snap-in markers - US-EMP (60X15) YE - 0828856



Snap-in markers, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 60 x 15 mm, Number of individual labels: 9

Snap-in markers - US-EMP (70X15) - 0830297



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 70 x 15 mm, Number of individual labels: 8

Snap-in markers - US-EMP (70X15) RD - 0830315



Snap-in markers, Card, red, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 70 x 15 mm, Number of individual labels: 8

Snap-in markers - US-EMP (70X15) SR - 0830314



Snap-in markers, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 70 x 15 mm, Number of individual labels: 8

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366

Accessories

Snap-in markers - US-EMP (8,8X15) - 0830293



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 8.8 x 15 mm, Number of individual labels: 88

Snap-in markers - US-EMP (8,8X15) RD - 0830428



Snap-in markers, Card, red, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 8.8 x 15 mm, Number of individual labels: 88

Snap-in markers - US-EMP (8,8X15) SR - 0830427



Snap-in markers, Card, silver, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 8.8 x 15 mm, Number of individual labels: 88

Snap-in markers - US-EMP (8,8X15) YE - 0830426



Snap-in markers, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 8.8 x 15 mm, Number of individual labels: 88