



- NOTES:
1. MATERIALS AND FINISHES:
BODY - BERYLLIUM COPPER, ALBALOY PLATING
CONTACT PIN - BERYLLIUM COPPER, GOLD PLATING
INSULATORS - PTFE, NATRUAL
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC - 6 GHz
C. VSWR: 1.15 @ DC - 3 GHz
1.20 @ 3 - 6 Ghz
3. MECHANICAL:
A. TEMPERATURE RANGE: -55° C TO 125° C
4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: "AMPHENOL RF, AD-SMAJHDEFIP-1, DATE CODE"

THIRD ANGLE PROJ.		REVISIONS			
REV	DESCRIPTION	DATE	ECN	APPR	
A	RELEASE TO MFG.	06-Aug-18	8787	BMG	



SCALE 5.000



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1°	MATERIAL		DRAWN		DATE		TITLE SMA JACK TO HD-EFI PLUG ADAPTER		Amphenol RF www.amphenolrf.com	
	SEE NOTES		B. GREENBAUM		11-Jun-18					
	REFERENCE		ENGINEER		DATE					
	EAR# 8375		B. GREENBAUM		11-Jun-18		SCALE: 10.0:1.0		SHEET 2 OF 2	
	REF: SMAF-DFIFI-AT5GP-50		APPROVED		DATE					
CONFIGURATION LEVEL: In Work		K. CAPOZZI		06-Aug-18		DWG SIZE		REV		
FINISH		CAD FILE				B		A		

DRAWING NO. AD-SMAJHDEFIP-1	
ITEM NO.	AD-SMAJHDEFIP-1
PART NO.	AD-SMAJHDEFIP-1

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.