



Part Number : 1731120281

Product Description : FCT High Power Contact, Male, Straight, Solder Cup, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, 30.0A, 12-10 AWG



Series Number : 173112

Status : Active

Product Category : D-Sub Contacts

Engineering Number : FMP105P103

Documents & Resources

Drawings

[1731120281_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[1731120008-PK-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Contacts
Series	173112
Description	FCT High Power Contact, Male, Straight, Solder Cup, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, 30.0A, 12-10 AWG
Contact Type	High Power
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	889056722940

Electrical

Current - Maximum per Contact	30.0A
-------------------------------	-------

Physical

Durability (mating cycles min)	500
Gender	Male
Material - Contact	Copper Alloy
Material - Plating Mating	Gold over Nickel

Material - Plating Termination	Gold over Nickel
Material - Retaining Clip	Copper Alloy
Net Weight	2.100/g
Orientation	Straight
Packaging Type	Bag
Plating min - Mating	0.800µm
Plating min - Termination	0.200µm
Temperature Range - Operating	-55° to +155°C
Termination Style	Solder Cup
Wire Size (AWG)	10, 12

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	FCT Mixed Layout Connectors

Application Tooling

Global

Description	Part Number
FCT Removal Tool for Size 8 Contacts	<u>1731121747</u>

This document was generated on Sep 10, 2025