F.MF16/12

TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories → Female Plugs

General Information

Extended Product Type:	F.MF16/12
Product ID:	1SNA113118R1700
EAN:	3472591131185
Catalog Description:	F.MF16/12 Female Plugs Grey
Long Description:	Each contact is numbered on the two elements of the housing.

Ordering

Color:	Grey
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	7.1 g

Technical

Function:	Female Plugs
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.22 ... 1.5 mm² Screw Clamp / Rigid 1x 0.22 ... 1.5 mm²
Rated Voltage (U_r):	750 V
Pollution Degree:	3
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Certificates and Declarations (Document Number)

CSA Certificate:	1SND164002A0200
Declaration of Conformity - CE:	1SSD235034C1001

Classifications

Object Classification Code:	X
ETIM 4:	EC002638 - Cable connector
ETIM 5:	EC002638 - Cable connector
ETIM 6:	EC002638 - Cable connector

Container Information

Package Level 1 Units:	10 piece

Downloaded from Arrow.com.

Package Level 1 Width:	155 mm
Package Level 1 Depth / Length:	200 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.071 kg
Package Level 1 EAN:	3472591131185
Package Level 2 Units:	500 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	150 mm
Package Level 3 Units:	18000 piece
Product Packing Type:	Bag



Downloaded from Arrow.com.