

Han-Snap Latching parts w. strain relief



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 000 9991
Specification	Han-Snap Latching parts w. strain relief
HARTING eCatalogue	https://b2b.harting.com/09330009991

Identification

Category	Accessories
Series	Han-Snap®
Type of accessory	Latching parts
Description of the accessory	With strain relief

Version

Pack contents	1 latching part with strain relief 1 latching part
---------------	---

Technical characteristics

Tightening torque	0.8 Nm
Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP20
Retention force	200 N Without guiding 300 N With guiding

Material properties

Material (accessories)	Polycarbonate (PC)
Colour (accessories)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50

Page 1 / 2 | Creation date 2024-03-13 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60068-2-6 Vibration (sinusoidal) IEC 60068-2-27 Shock
----------------	--

Commercial data

Packaging size	10
Net weight	19.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140050686
ETIM	EC002939
eCl@ss	27440392 Connector (accessories)