
YAE22N66F, Nylon Fork, 26-20 AWG, #4-6 Stud



By Burndy
Catalog # YAE22N66F

Nylon Fork Terminal, 26-20 AWG, #4-6 Stud, Multi-Finger Insulation Grip, Fork Tongue, Smooth Funnel Entry, Bulk Package

Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulations
- Brazed seam provides a stronger, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance, and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability and holding power
- Smooth funnen entry for easy wire insertion

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	26 - 20 AWG
Conductor - Copper Str Aircraft Size	• AN 26 • AN 22 • AN 20
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	24 AWG - 20 AWG
Conductor - Copper Str Size	20 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current

Voltage - Maximum	600 V

Dimensions

Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Bolt Size fraction	#4 - #6
Dimension - B Length fraction	10/91 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.27 in
Dimension - B Length inch	0.11 in
Dimension - N inch	0.12 in
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	0.8 in
Dimension - Strip Length inch	5/32 in
Dimension - Stud Size inch	• #4 • #5 • #6

General

Plated	Yes
Color Code	Amber
Product Family	COMPRESSION
Insulation Type	Nylon
Trade Name	INSULUG™
Physical Attribute - Tongue Type	Fork
Product Type	Terminal
UPC	781810804049
Insulation	Y
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810804049
UPC 14 Digit GTIN	00781810804049

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	99999
Carton Quantity	1000
Packaging Type	Bulk

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved

Downloaded from Arrow.com.