




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.		REVISIONS	
REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	3/10/2006	
A1	Change Part Number	2/11/106	
A2	CHANGE FROM BOOT TO MOLDING	03/03/07	
A3	Add 1 FT Part Number	19/09/07	
A4	Add 8 FT Part Number	20/MAR/2014	



LENGTH & P/N Table

LENGTH	P/N	Cable Color
1FT ±1 inch	MP-SERJ45UNNK-001	BLACK
3FT ±1 inch	MP-SERJ45UNNK-003	BLACK
5FT ±2 inch	MP-SERJ45UNNK-005	BLACK
7FT ±2 inch	MP-SERJ45UNNK-007	BLACK
8FT ±2 inch	MP-SERJ45UNNK-008	BLACK
10FT ±3 inch	MP-SERJ45UNNK-010	BLACK
14FT ±3 inch	MP-SERJ45UNNK-014	BLACK
25FT ±4 inch	MP-SERJ45UNNK-025	BLACK
50FT ±8 inch	MP-SERJ45UNNK-050	BLACK
75FT ±8 inch	MP-SERJ45UNNK-075	BLACK
100FT ±8 inch	MP-SERJ45UNNK-100	BLACK



PIN OUT: T568B	
PLUG 1	PLUG 2
PIN 1	PIN 1
PIN 2	PIN 2
PIN 3	PIN 3
PIN 4	PIN 4
PIN 5	PIN 5
PIN 6	PIN 6
PIN 7	PIN 7
PIN 8	PIN 8



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		E&R NO.		Amphenol Cables on Demand	
DECIMALS	ANGLES	DRAWN	DATE	20 VALLEY ST. ENDICOTT, NY 13760	
X	± X°	LF	20/MAR/2014	ASM CBL RJ45/RJ45 CAT.5E	
XX	±.XX	CHECKED	BA	4PR PATCH CORDS	
XXX	±.XXX	RESP ENG			
THIRD ANGLE PROJECTION		WFG ENG			
C&D FILE:		SIZE	DWG. NO.	REV.	
		A	MP-5ERJ45UNNK-XXX	A4	

NOTES: UNLESS OTHERWISE SPECIFIED