

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	26MAY2015	DW	CW
	B	ECR-20-008190	10AUG2020	WQR	CW
	B1	ECR-21-105138	29JUN2021	WQR	CW


NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: POWDER COATED, GREY
DEGREE OF PROTECTION: IP65 (MATED)

注释：
1. 技术参数：
上壳材料： 铝合金
表面处理： 粉末涂层，灰色
防护等级： IP65(配合)










TYPE 1: LOW CONSTRUCTION, SIDE ENTRY
WITH STAINLESS STEEL LOCKING



TYPE 2: LOW CONSTRUCTION, TOP ENTRY
WITH STAINLESS STEEL LOCKING
OTHER SPEC REFER TO TYPE 1

PART NUMBER	TYPE	DESCRIPTION	IG1	IG2
T1250163121-000	TYPE 1	H16B-TSBS-PG21	PG21	-
T1250163125-000		H16B-TSBS-M25	M25	-
T1250163132-000		H16B-TSBS-M32	M32	-
T1260163116-000	TYPE 2	H16B-TGBS-PG16	-	PG16
T1260163121-000		H16B-TGBS-PG21	-	PG21
T1260163125-000		H16B-TGBS-M25	-	M25

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL -
-

FINISH -
-

DWN David Wang 26MAY2015
CHK Chris Wang 26MAY2015
APVD Xiang Xu 26MAY2015
PRODUCT SPEC 108-137013
APPLICATION SPEC 114-137013
WEIGHT -

TE Connectivity

NAME H16B-TSBS/TGBS-M/PG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C⇨T12X01631XX000	-

Customer Drawing | SCALE 1:1 | SHEET 1 OF 1 | REV B1

1471-9 (3/13)

printed on 2 Jul 2021 11:09 (China Standard Time) from TE343646

Downloaded from Arrow.com