
For insertion / removal of two-tiered type (Pitch: 2.54 mm)

OY series (10pcs/pack)


- This is used for mounting PC boards by two-tiered installation.
- Pitch: 2.54 mm, 20P connected
- Please cut it by using a mold cutting nipper (Part number: MOC-3)
- Material Pin: Brass, Finish: Gold plating over nickel base
  Resin: PBT red, black (We offer two colors.) (UL94V-0)
- Rated current : 3A
- Insulation resistance : 500M Ω or over
- Withstand voltage : 1000V AC,DC per minute
- Operating temperature range: − 40 to + 125℃
- Adaptive socket: PD-1,PD-10,PM-1,PM-10


20P connected

■ How to order:


OY-002 BLACK ← If this is not specified, RED will be specified.


■ Example of usage



Part No.	A	B	H	Printed board fitting hole diameter
OY-002	0.55	0	8.18	ϕ 0.8
OY-003	1.2	1.82	10	ϕ 0.8
OY-004	1.2	4.32	12.5	ϕ 0.8
OY-005	1.2	6.82	15	ϕ 0.8
OY-006	1.2	11.82	20	ϕ 0.8

* The dimension H indicates the distance between the main board and the slave board when PD-1, PD-10 or PM-1, PM-10 is used.





Please contact us when you need the number of poles larger than 20 pins connected.

Downloaded from Arrow.com.