Specification Sheet

Part Number: 151-02189



Integrated design allows for easy insertion by hand.

1.5–2mm panel thickness range allows for multiple applications.

Double-compression design that accommodates various sizes of wire and cable.

Presents a high extraction force for withstanding extreme conditions.

Low Profile 90° Metal Edge Clip, 1.5–2.0mm Panel Thickness, 6–6.2mm Cable Range, SS304, 100/bg

Article Number	151-02189
Type	MSC90
Color	Metal (ML)
Quantity Per	pack
Product Description	HellermannTyton's 90-Degree Metal Edge Clip provides an excellent alternative to managing wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, this edge clip also has a high extraction force. The 90-degree configuration secures cables to a panel in a perpendicular orientation. Metal construction tolerates extreme environments, and a low-profile design allows the clip to be installed on a wide variety of module edges.
Short Description	Low Profile 90° Metal Edge Clip, 1.5–2.0mm Panel Thickness, 6–6.2mm Cable Range, SS304, 100/bg

Downloaded from Arrow.com.

Global Part Name	MSC90-SS304-ML
Length L (Imperial)	0.73
Length L (Metric)	18.44
Fixation Method	Edge Clip
Width W (Imperial)	0.460
Width W (Metric)	11.57
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	4.1
Bundle Diameter Max (Imperial)	0.28
Bundle Diameter Max (Metric)	7.0
Depth D (Imperial)	0.445
Depth D (Metric)	11.303
Panel Thickness Min (Imperial)	0.06
Panel Thickness Max (Imperial)	0.08
Panel Thickness Min (Metric)	1.5
Panel Thickness Max (Metric)	2.0

Downloaded from Arrow.com.

Material	Stainless Steel (SS304)
Material Shortcut	SS304
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
BABA Compliant	YES
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100

Downloaded from Arrow.com.

Customs Number	7326908695

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.