Part Number : 570316000
Product Description : Hand Extraction Tool
Series Number : 57031
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents and Resources

Tooling Specifications

ATP-57031-6000E-001.pdf

ATP-57031-6000JE-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	57031
Description	Hand Extraction Tool
Function	Extraction
Geographic Area	Japan
Level of Automation	Manual
Product Name	N/A
Tool Type	Extraction Hand Tool
UPC	800753633414
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	4.350/g

Applicable Parts

Downloaded from Arrow.com.

Description	Part Number
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, Double 22+22 or Single 24-18 AWG, Reel	39000038
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 28-22 AWG, Reel	39000046
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 28-22 AWG, Bag	39000047
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, Double 22+20, 22+18, 20+20 or Single 16 AWG, Reel	39000077
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 16 AWG, Bag	39000078
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 24-18 AWG, Bag	39000039
Mini-Fit Male Crimp Terminal, Matte Tin (Sn) Plated Brass, Double 22+22 or Single 24-18 AWG, Reel	39000040
Mini-Fit Male Crimp Terminal, Matte Tin (Sn) Plated Brass, 28-22 AWG, Reel	39000048
Mini-Fit Male Crimp Terminal, Matte Tin (Sn) Plated Brass, 28-22 AWG, Bag	39000049
Mini-Fit Male Crimp Terminal, Matte Tin (Sn) Plated Brass, Double 22+20, 22+18, 20+20 or Single 16 AWG, Reel	39000081
Mini-Fit Male Crimp Terminal, Matte Tin (Sn) Plated Brass, 16 AWG, Bag	39000082
Mini-Fit Male Crimp Terminal, Matte Tin (Sn) Plated Brass, 24-18 AWG, Bag	39000041

Downloaded from Arrow.com.

Downloaded from Arrow.com.