Heyco®-Tite Metallic Liquid Tight Cordgrips

Straight-Thru, NPT Hubs


The Ultimate in Liquid Tight Strain Relief Protection




CABLE DIA. RANGE Minimum in.	Minimum mm.	Maximum in.	Maximum mm.	PART NO.	DESC.	Gland Color	NPT HUB SIZE	A Clearance Hole Dia. in.	A mm.	B Sealing Nut HEX in.	B mm.	C Body Nut O.D. in.	C mm.	D Overall Length* in.	D mm.	E Exposed Length* in.	E mm.
Steel																	
.150	3,8	.250	6,3	**9760**	CG 50A-250	Red											
.250	6,3	.350	8,9	**9761**	CG 50A-350	White											
.350	8,9	.450	11,4	**9762**	CG 50A-450	Blue	1/2	.875	22,2	1.03	26,2	.94	23,8	1.31	33,3	.81	20,6
.450	11,4	.550	14,0	**9763**	CG 50A-560	Green											
.550	14,0	.650	16,5	**9764**	CG 50A-650	Brown											
.150	3,8	.250	6,3	**9766**	CG 75A-250	Red											
.250	6,3	.350	8,9	**9767**	CG 75A-350	White											
.350	8,9	.450	11,4	**9769**	CG 75A-450	Blue	3/4	1.109	28,2	1.03	26,2	1.18	29,9	1.31	33,3	.81	20,6
.450	11,4	.550	14,0	**9770**	CG 75A-560	Green											
.550	14,0	.650	16,5	**9771**	CG 75A-650	Brown											
.650	16,5	.750	19,0	**9772**	CG 75B-750	Orange	3/4	1.109	28,2	1.27	32,3	1.18	29,9	1.56	39,7	1.03	26,2
.750	19,0	.850	21,6	**9773**	CG 75B-850	Purple											
Zinc Die-Cast																	
.190	4,8	.250	6,3	**9776**	CG 11												
.260	6,6	.375	9,5	**9777**	CG 12	N/A	1/2	.875	22,2	1.00	25,4	.94	23,8	1.20	30,5	.80	20,3
.375	9,5	.450	11,4	**9778**	CG 13												

*May vary slightly depending on cable diameter.

Steel



Zinc Die-Cast



Steel:

- **Zinc plated steel construction** for superior protection of flexible cables.
- Compact design allows fittings to be consecutively ganged–no skipping knockouts–and occupy less real estate.
- Galvanized steel pressure ring prevents distortion of the grommet when the sealing nut is tightened.
- Neoprene rubber grommet ensures a permanent rain-tight seal around the cable.
- Body and sealing nut are made of corrosion resistant machined steel. Zinc plated with special brighteners for an attractive finish.
- Color coded label system identifies the cordgrips by wire range/grommet opening.
- For use in clearance or threaded holes.
- Multiple cable sizes with 1/2˝ to 3/4˝ NPT hubs, cover a flexible cord diameter range of .150˝ (3,8 mm) to .850˝ (21,6 mm).
- Temperature Rating: 221°F (105°C).
- DFARS Compliant



Zinc Die-Cast:

- **Zamac #3 construction** for protection of flexible cables.
- For use in clearance or threaded holes.
- We recommend using the smallest maximum diameter range cordgrip that will fit your application.
- Temperature Rating: 140°F (60°C).
- DFARS Compliant

Downloaded from Arrow.com.