
C-171507



	PARTS NUMBER	STUD	H DIMENSION	INS. DIA
	171507-1	1/4	6.73	2.03 ~ 3.18
	-2	5/16	8.33	2.03 ~ 3.18
OBSOLETE	-3	1/4	6.73	2.66 ~ 3.56
OBSOLETE	171507-4	5/16	8.33	2.66 ~ 3.56

LTR	REVISION RECORD	DR.	CHK.	DATE
G	OBSOLETE	Y.O	N.Y	14APR17
F	Change Applicable Body	Y.O	N.Y	23JAN17
E	REVISED (P-DWG REV-D)	Y.Y	N.Y	6/Feb/25
D	REVISED (P-DWG REV-C)	S.O	Y.Y	11/Feb/25
C	ADDED MARK	H.S	Ari	9/11/25
B	REVISED (P-DWG REV-B)	H.S	Ari	7/1/25
A	REVISED (P-DWG REV-A)	H.S	K.M	4/1/25
C	SUPERSEDED P-DWG REV-C 31 25	[illegible]	[illegible]	10/1/25
H1	REVISED PER ECR-25-253648	SA	MDP	13AUG 2025
H	REVISED PER ECR-17-017886	E.T	N.Y	08DEC17

© 1975 BY AMP JAPAN, LTD. ALL RIGHTS RESERVED AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING

参考図面 CUSTOMER COPY REFERENCE ONLY

MATERIAL COPPER 電気銅
PLATING TIN 錫めっき
WIRE RANGE 0.26 ~ 1.04 mm² AWG 22-18
SPECIFICATION 参考照
SCALE 4-1
SIZE A
DRAWING NO. C-171507
REV. H1
TE CONNECTIVITY
CLASS —
TYPE プリインシュレイテッド・ダイヤモンドグリップ
DRAWN [illegible] 10/Oct/72
CHECKED [illegible]
APPROVED [illegible]
TITLE 丸型 端子 WIRE TERMINAL ASSEMBLY

4

AF-J 310-1
REV. 7-72

Downloaded from Arrow.com.