TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.25
.XX	±0.13
.XXX	±0.05

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.

ISSUE NUMBER	
ORIGINAL	1



NOTES:
CURRENT RATING: 2A AC/DC
VOLTAGE RATING: 100V AC/DC
TEMPERATURE RATING: -25°C ~ 85°C
(CONTACT RESISTANCE: 10mΩ MAX.)
HOUSING RESISTANCE: 1000MΩ min.
WITHSTANDING VOLTAGE: 800V AC / 60s
HOUSING MATERIAL: NYLON PA66, UL94V-0





140 SERIES FEMALE CRIMP CONTACT HOUSING

ACAD REFERENCE NO.:	140 Assembly		
DRAWN: C.B		DATE: April 3, 2020	
CHECKED:		DATE:	
SCALE: 5:1		SHEET 1 OF 1	
DRAWING NUMBER:	140 Assembly		ISSUE 1
PART NUMBER:	140-508-210-011		

EDAC INC
TORONTO, ONTARIO
CANADA
YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

RoHS COMPLIANT

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

Downloaded from Arrow.com.