















Similar to illustration

Color coding acc. to DIN VDE 47100		14 poles flat connector
		Pin number
White		1
Brown		2
Green		3
Yellow		4
Grey		5
Pink		6
Blue		7
Red		8
Black		9
Violet		10
Grey-Pink		11
Red-Blue		12
White-Green		13
Brown-Green		14

**Short description:**  
WAGO's 14-pole interface cables transmit the signal one-to-one from the 14-pole connector and are available in 1-, 2- and 3-meter lengths. These cables are suitable for system wiring when paired with 857-981 and 857-982 Interface Adapters.

Notes	
Note	When using more than 10 wires, the maximum current per wire must be reduced to 0.7 A.

Electrical data	
Operating voltage	≤ 35 VDC
Current per wire (max.)	1 A



Connection data

Cable type	LiYY	Connection 1	
Color code	per DIN VDE 47100	Pluggable connector	Pluggable connector per DIN 41651; fe- male connector
		Pole number 1	14
		Connection type 1	System
		Wire cross-section	0.14 mm²

Connection 2	
Connector 2	Pluggable connector per DIN 41651; fe- male connector
Pole number 2	14
Connection type	System

Physical data

Cable length	3 m
--------------	-----

Material data

Fire load	0 MJ
Weight	165 g

Environmental requirements

Ambient temperature (operation)	-25 ... +70 °C
---------------------------------	----------------

Commercial data

Product Group	30 (WAGO France)
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	FR
GTIN	4050821081647
Customs tariff number	85444290900

Product classification

UNSPSC	26121629
eCl@ss 10.0	27-06-03-11
eCl@ss 9.0	27-06-03-11
ETIM 9.0	EC001855
ETIM 8.0	EC001855
ECCN	NO US CLASSIFICATION



Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 706-753/300-300	

Documentation

Bid Text			
706-753/300-300	26.11.2018	docx 14.91 KB	
706-753/300-300	19.02.2019	xml 3.15 KB	

CAD/CAE-Data

CAE data	
WSCAD Universe 706-753/300-300	

1 Compatible Products

1.1 Optional Accessories

1.1.1 Interface module

1.1.1.1 Interface adapters



[Item No.: 857-981](#)  
Interface adapter; 14-pole; High-side switching input



[Item No.: 857-982](#)  
Interface adapter; 14-pole; High-side switching output

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](https://www.wago.com)