

Obsolete

Recommended Alternate Part No. : CLF7045T-680M-D (Interchangeability is not guaranteed.)

Product Status

Discontinue Issue Date : May.18, 2017

Last Purchase Order Date : Mar.29, 2019

Last Shipment Date : Sep.30, 2019

Applications

Commercial Grade

Wire WoundWire Wound

FeatureShieldMagnetic Shield

Ferrite CoreFerrite Core

Series | Type

CLF

Brand

TDK

Environmental

RoHS REACH

Compliance



Lead Free

**Size**

Length(L)	7.20mm ± 0.20 mm
Width(W)	6.90mm ± 0.20 mm
Thickness Height	4.50mm ± 0.30 mm
Recommended Land Pattern (A)	1.70mm Nom.
Recommended Land Pattern (B)	4.40mm Nom.
Recommended Land Pattern (C)	2.20mm Nom.

Electrical Characteristics

Inductance	68 μ H $\pm 20\%$ at 100kHz
Rated Current (L Change) [Typ.]	1.1A (10% Down)
Rated Current (L Change) [Max.]	
Rated Current (Temperature Rise) [Typ.]	950mA (30°C Rise)
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	210m Ω
DC Resistance [Max.]	252m Ω
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	
Self Resonant Frequency [Typ.]	
Q [Min.]	
Q [Typ.]	

Other

Operating Temp. Range	-40 to 105°C (Including Self-Temp. Rise)
-----------------------	--

! Images are for reference only and show exemplary products.







! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

Soldering Method	Reflow Iron Soldering
AEC-Q200	NO
Packing	Punched (Paper)Taping [330mm Reel]
Package Quantity	1000pcs
Weight	0.8g

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)




! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.



! All specifications are subject to change without notice.

Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Associated Images



! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.