



Part Number : [26033081](#)
Product Description : KK 3.96mm Crimp Terminal
Housing, Use With Trifurcon Terminals, 8 Circuits,
Natural
Series Number : 6442
Status : Active
Product Category : Connector Housings
Engineering Number : 6442-08-Z



Documents & Resources


Drawings
[026033081_sd.pdf](#)

3D Models and Design Files
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications
[PS-40-02-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	6442
Description	KK 3.96mm Crimp Terminal Housing, Use With Trifurcon Terminals, 8 Circuits, Natural
Application	Power, Wire-to-Board
Comments	Replacement is V-0 instead of V-2
Product Name	KK 396
UPC	800753587281

Agency

CSA	LR19980
-----	---------

Physical

Circuits (maximum)	8
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	2.080/g
Number of Rows	1

Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Stackable	No
Temperature Range - Operating	See Product Specification

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Molex 3.96mm pitch KK headers

Use with Part(s)

Description	Part Number
Pre-Crimped Lead KK Plus 396 Female-to-KK Plus 396 Female, Tin (Sn) Plating, 150.00mm Length, 18 AWG, Black	<u>797582145</u>
Pre-Crimped Lead KK Plus 396 Female-to-KK Plus 396 Female, Tin (Sn) Plating, 300.00mm Length, 18 AWG, Black	<u>797582146</u>
Female Crimp Terminals for 3.96mm Pitch Housings	<u>45570</u>
KK Trifurcon Female Crimp Terminals	<u>6838</u>
KK Trifurcon Female Crimp Terminals	<u>7258</u>

This document was generated on Sep 25, 2025