Datasheet for part number HDX-WK1M0-12WMA

Our Catalog Part Number: HDX-WK1M0-12WMA
Our Global Manufacturing Part Number: 155911-0013
Brand: Cannon Product Category: HDx Product Line: HDx Series: HDX

Product Datasheet	
Series	HDXW High Density Series
Connector Type	Receptacle, In Line
Coupling Style	Break Away
Shell Style	In Line
Shell Material	Brass Alloy
Plating	Ruthenium over Electroless Nickel
Contact Arrangement	0-12
Contact Quantity	12
Contact Type	Solder Cup
Contact Gender	Socket
Contact Size	Combo/Mixed 10 x 0.3mm + 2 x 0.7mm
Polarization	Brown Color Code
Receptacle Earth Tag	No
Wire Accommodation	10 x 28 AWG + 2 x 22 AWG
Currrent Rating	10 x 1A + 2 x 5A
Operating Voltage	250VDC
Operating Temperature	-51°C to +125°C
Durability	5,000 mating cycles
Salt Spray	96 Hrs Salt Fog
Water Immersion	20 meters for 120 mins

Specifications and dimensions subject to change.

Downloaded from Arrow.com.