

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 45U, Black, 2124H x 750W x 1070D mm

AR3155

Overview

Presentation	This enclosure is designed to meet current IT market trends and applications ranging from high density computing and networking to broadcast and audio-video. The rack height is 45U, 750mm Wide x 1070mm Deep . It provides a reliable rack-mounting environment for mission-critical equipment.
Lead time	Usually in Stock

Main

Product or component type	Rack enclosure
Number of rack unit	45U
Provided equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels

Physical

Height	2124 mm
Width	750 mm
Depth	1070 mm
Net weight	155 kg
Colour	Black
Mounting preference	No preference
Mounting mode	Not rack-mountable
Maximum mounting depth	914.9 mm
Minimum mounting depth	261.9 mm
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	1020.6 kg dynamic 1701.0 kg static

Conformance

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	224 cm
Package 1 Width	132 cm
Package 1 Length	85 cm
Package 1 Weight	172.3 kg

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Total lifecycle Carbon footprint	523

Use Better	
Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
[EU RoHS Directive](#)	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	[REACH Declaration](#)
Use Again	
Repack and remanufacture	
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative









