MICRO SWITCH
FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - TOGGLE FLUSH KEY

CATALOG LISTING
4TP8-12

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CIRCUIT MADE WITH ROCKER DEPRESSED ON

LUG SIDE (MAINTAINED POSITION)	CENTER (MAINTAINED POSITION)	OPPOSITE LUG (MAINTAINED POSITION)



ELECTRICAL DATA

15A-125, 250 OR 277 VAC
1/2HP-125VAC; 1HP-250, 277VAC
5A-125VAC "L" CODE L191

NOTES
1 - MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
2 - THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F
3 SCREWS FURNISHED UNASSEMBLED

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. mm	TOL. mm/m	DIM. in	TOL. mm/m
NO PLACES	X	1/.04		
ONE PLACE	X.X	0.4/.016	X.X	0.4/.02
TWO PLACES	X.XX	0.15/.006	X.XX	0.36/.015
THREE PLACES			X.XXX	0.13/.005
ANGLES				

DESIGN UNITS: IN METRIC ☐ US CUSTOMARY ☒

WEIGHT .22 LBS APPROX

CATALOG LISTING 4TP8-12 PAGE 1 OF 1
ISSUE M 5
REPLACES
RELEASE NO. PR-12222
CHECK

REVISIONS
A C060064 S. J. S. 20 AUG 86
B C077697 TSM 15 JUN 94
C CO 79047 S A D 12 JAN 95
D CO-94417 CSL 24 NOV 99

J	16 JUN 83	J A P	
C	17 JUNE 83	C E C	
K	20 JUNE 83	J C	

FORMTEK FO-52854-C

Downloaded from Arrow.com.