



[My Cart](#)



[My Part Lists](#)

[Sign In/Register](#)



[English \(Change\)](#)

Have a Question?

Chat with a Product
Information Specialist



What can we help you find?



[Products](#)

[Industries](#)

[Resources](#)

[About TE](#)

[My Account](#)

[Innovation](#)

[Support Center](#)


[Home](#) > [Products](#) > [Resistors](#) > [Product Feature Selector](#) > Product Details

DPL12SH2424A25K2 Product Details

[Share](#)

[Print](#)

[Email](#)



DPL12SH2424A25K2
(2-1879749-1)

TE Internal Number: 2-1879749-1

Active

Variable Resistors



Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Encoder
- Resistor Type = LED Encoder
- DPL12 Series
- Sections = Single
- Not Sealed

[View all Features](#)

Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)



[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [1309350_PASSIVE_COMPONENT](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Encoder
- Resistor Type = LED Encoder
- Series = DPL12
- Sealed = No
- Mount Angle = Horizontal
- Termination Type = PCB Terminations

Termination Features:

- Termination Post Orientation = 5.0 x 2.5

Body Features:

- Switch Type = Push-Push SPDT, 0.5mA
- Shaft Style = Knurled, M7 x 5mm Bush
- Package, Component Size = 14.0 x 13.2

Configuration Features:

- Sections = Single
- Adjustment Location = Side
- Adjustment Style = Spindle With Push Switch
- Operating Function = Continuous

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not reviewed for lead free solder process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Citec

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events &
Technology Updates

Enter your email address

