

C-FCI 1,5/M4 - Fork-type cable lug



3240034

<https://www.phoenixcontact.com/us/products/3240034>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fork-type cable lug, red, 0.5 - 1.5 mm², M4

Your advantages

- The fork-type cable lugs without plastic sleeve feature a hard-soldered neck. In conjunction with the CRIMPFOX-RC ... and CRIMPFOX-RCI ... pliers they can be used to achieve maximum conductor pull-out forces
- The insulated versions are halogen-free and feature "EASY ENTRY" technology

Commercial data

Item number	3240034
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BH34
Product key	BH3441
GTIN	4046356451116
Weight per piece (including packing)	0.692 g
Weight per piece (excluding packing)	0.663 g
Customs tariff number	85369010
Country of origin	CN

C-FCI 1,5/M4 - Fork-type cable lug

3240034

<https://www.phoenixcontact.com/us/products/3240034>




Technical data

Product properties

Product type	Connector
Product property	With “Easy Entry” system
	Brazed
	PA-insulated

Dimensions

Dimensional drawing	
Width	7.2 mm
Sleeve length	22 mm
Length of the insulating material sleeve	10.5 mm
Maximum stripping length	7 mm
Distance from the center to the insulating material sleeve	7.2 mm
Min. material thickness	0.75 mm
Inner dimensions of the insulating collar	4.1 mm

Internal dimensions

Internal diameter	4.3 mm
-------------------	--------

Material specifications

Color	red (RAL 3001)
Material	Copper
Flammability rating according to UL 94	V2
Coating	tin-plated
Insulating material	PA
Components	halogen-free

Mechanical properties

Technical data	
Sleeve length	22 mm

C-FCI 1,5/M4 - Fork-type cable lug


3240034

<https://www.phoenixcontact.com/us/products/3240034>



Drawings

Dimensional drawing



C-FCI 1,5/M4 - Fork-type cable lug

3240034

<https://www.phoenixcontact.com/us/products/3240034>



Classifications

ECLASS

ECLASS-13.0	27400204
ECLASS-15.0	27400204

ETIM

ETIM 9.0	EC001052
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

C-FCI 1,5/M4 - Fork-type cable lug



3240034

<https://www.phoenixcontact.com/us/products/3240034>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com