




Snapper Hose Clips for Tubes and Harnesses SNP14A

SNP-Series, Article number: 190-00302



Images (7)



Features

- Releasable and reusable plastic hose clamps
- Self-locking
- Releasable by giving a lateral movement to the 'head'
- Installation by hand possible
- Installation with processing tool for a secure tensioning
- For higher operating temperatures: Glass Filled PA66

Certifications & Approvals



Application

Our SNP range can be used as an alternative to metal hose clamps. Snapper can be used in markets as diverse as automotive, agriculture, white goods, venting systems, pumps and hydraulic systems to medical engineering.


More products in this product group

[Snapper Hose Clips for Tubes and Harnesses >](#)

Base Data

Application Tool	ASNP2-22, ASNP24-70
Colour	White (WH)
Fixation Method	Plug-in mounting
GLOBAL PART DESCRIPTION	SNP14A-POM-WH
Pack Cont.	100
Package Quantity per	bag
Product Family	SNP-Series
Product Group	Snapper Hose Clips for Tubes and Harnesses
Variant	Closed

Product Dimensions



Wall (WT)	1.75 mm
Wall (WT)	.069 "
Width (W) max.	29.39 mm
Width (W) min.	20.45 mm
Width (W) min.	0.805 "
Width (W2)	5.92 mm
∅ D max.	0.81 "
∅ D max.	20.57 mm
∅ D min.	18.14 mm
∅ D min.	0.714 "

Material and Specifications



Flammability	UL 94 HB
Material	Polyacetal (POM)
Operating Temperature - °C	-40 °C to +85 °C
Specifications	RoHS
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No

Logistics and Packaging



More Information



ETIM 5.0	EC000127
ETIM 6.0	EC000127
UNSPSC Key	39121702

Competences





Ratchet P-Clamp for mounting cables and hoses

Discover the versatile addition to our range of metal and plastic cable clamps: the Ratchet P-Clamp. The innovative design makes it possible to fix wires, cables, hoses and pipes on a single mounting point in two separate work steps. Installers and maintenance engineers no longer have to hold the bundle and the clamp awkwardly in one hand whilst fixing them securely with the other.

[P-Clamp >](#)

Accessories



ASNP2-22
191-02220
Snapper Tools



ASNP24-70
191-24700
Snapper Tools

Similar products



SNP1(E)
190-00024
Snapper Hose Clips for
Tubes and Harnesses



SNP1.25
190-00029
Snapper Hose Clips for
Tubes and Harnesses



SNP1.25
190-00030
Snapper Hose Clips for
Tubes and Harnesses



SNP1.25
190-00027
Snapper Hose Clips for
Tubes and Harnesses



SNP1.25
190-00028
Snapper Hose Clips for
Tubes and Harnesses



SNP1.5
190-00336
Snapper Hose Clips for
Tubes and Harnesses

[Show all >](#)

Stay in touch with us!



Global Company

About us
Worldwide
Philosophy
Environment & Quality
Corporate Social
Responsibility
Product Development
E-Business
ACADEMY
Careers
MADE FOR REAL

Products

Product overview
Cable Ties and Fixings
Insulation
Cable Protection Systems
Electrical Installation
Identification Systems
Application Tooling
Connectivity

Competences

Cable Ties
Heat Shrink Tubing
Industrial Identification
and Self-Adhesive Labels
Cable Protection
Conduits
Electrical Installation
Electrical tape
Wire connectors
Cable rods
Downlight covers
Cable jointing
Gel-filled cable joints
Cable Tie Guns
Connectivity Products
RFID tracking
Cable tie mounts
Thermal Transfer Printer
P-Clamp
Wiring ducts
Cable clips for edges

Markets & Industries

Automotive Industry
Solar plants
Wind turbines
Shipbuilding
Panel building
Rail industry
Food Industry
Chemical Industry
Aerospace Industry
Defence Industry

Media Centre

Videos
Product Catalogue
2018/2019
Automotive Catalogue
2016/2017
Connectivity Catalogues
2016/2017
Brochures
Software & Drivers
Helatag & Helafix
Templates
Manuals & Operating
Instructions

Cable management high
temperature
applications

Events

Update: 16/09/2018

You can easily accept or reject the cookies on this site by choosing one of the following links:

[I accept cookies](#)

[I refuse cookies](#)

[Privacy](#)

[Contact](#) [Terms of Service](#) [Imprint](#) [Privacy Policy](#)

[statement](#)