



BIBS3505, Single Sided Five Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBS3505](#)



MULTI-PORT Single-Sided Entry.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

General

Catalog Number	BIBS3505
Hex Key	5/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	5
Physical Attribute - Number of Screws	10
Physical Attribute - Screw Type	Allen
Temperature Rating	194
Trade Name	UNITAP™
UPC	781810133507
UPC 14 Digit GTIN	00781810133507

Dimensions

Dimension - Height inch	2.50 in
Dimension - Height mm	64 mm
Dimension - Width inch	2.32 in
Dimension - Width mm	59 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size Range	10 AWG - 350 kcmil
Conductor - Copper Str Size Range	10 AWG - 350 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size

Certifications And Compliance

Buy America(n) Qualified	BABA Compliant (All status valid till December 2024)
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	40
Minimum Pack Quantity	1

Product Assets

- [3D Models - BIBS3505_MODEL-IGES](#)
- [3D Models - BIBS3505_MODEL-PDF](#)
- [3D Models - BIBS3505_MODEL-STEP](#)
- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BIBS_Lineart](#)
- [Sales Drawings - sc210991-13](#)
- [Specifications - BIBS3505](#)

