RoHS
Halogen-Free

| Edition | Modifier | Date | Description | ECN No. |
|---|---|---|---|---|
| | | | | |
| | | | | |




| Item | Code | Spec | |
|---|---|---|---|
| NO of PIN | N | 10 | |
| Pitch | P | 0.5±0.05 | |
| Total Length | L | 127±1.5 | |
| Margin | M | 0.5±0.05 | |
| **Thickness** | T | 0.3±0.03 | |
| Strip Length | S1 | 3.5±0.5 | |
| | S2 | 3.5±0.5 | |
| Supporting Length | D1 | 6.0±1.0 | |
| | D2 | 6.0±1.0 | |
| Total Pitch | TP | 4.5±0.05 | |
| Total Width | W | 5.5±0.05 | |
| Conductors | Width | 0.3±0.03 | |
| | Thickness | 0.035±0.005 | |
| | Plated | Sn(1um) | Min |
| Film | White | 0.06mm | |
| | White | 0.06mm | |
| Supporting | Blue | 0.225mm | |
| UL NO. | **UL20890(105℃ 90V)** | | |

Processing requirement:




| NO. | Specification description | Number | Remarks |
|---|---|---|---|
| | | | |
| 1. | | | |

# CnC Tech, LLC

Industrial Cable and Connector Technology

| | | | |
|---|---|---|---|
| DRAWN BY: | DATE: 2018/07/20 | DESCRIPTION: 10-127-0.5-3.5/3.5-6/6-A-Tin | |
| CHECKED BY: | SHEET 1 of 1 | ITEM NO. 310-10-0127 | |
| APPROVED BY: | SCALE 1:1 | REV. A/0 | UNIT: mm |

Downloaded from Arrow.com.