




Have a Question?
Chat with a Product
Information Specialist

What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

1971885-1 Product Details

Share Print Email



Active
[View 3D PDF](#)

PCB Mounted Jacks - Single Port,
Multi-port and Stacked
D-SHAPE SMT VERTICAL MINI IO RECEPTACLE
1971885-1

TE Internal Number: 1971885-1

Product Highlights [View All](#)

- Connector
- Preloaded
- Single Port Configuration
- 2 x 8 Jack Configuration
- Jack Type = Industrial Mini

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through
Distributor](#)

- Documents
- Features
- Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Connector
Jack Type	Industrial Mini
PCB Mounting Orientation	Top Entry (Vertical)
PCB Mount Style	Surface Mount
LED	Without
Grounding Options	Without
Panel Stops	Without
Keyed	No
Profile	Standard
Mechanical Attachment	
Panel Mount Retention	Without
Termination Features	
Termination Method to PC Board	Solder

Housing Features	
Housing Material	Thermoplastic
Housing Color	Black
Configuration Features	
Preloaded	Yes
Port Configuration	Single
Jack Configuration	2 x 8
Number of Positions	8
Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not reviewed for lead free solder process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0

Dimensions		Product Availability	
Height (mm [in])	14.48 [0.570]	Region	Asia, North America
PCB Thickness, Recommended (mm [in])	1.60 [0.063]	Other	
Contact Features		Brand	TE Connectivity
Solder Tail Contact Plating	Tin over Nickel		
Contact Plating, Mating Area, Material	Gold		
Contact Base Material	Copper Alloy		

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy
- Global Accessibility Statement

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

