



Color:   white

Technical data

|                             |  |
|-----------------------------|--|
| Suitable                    | for cable diameter 4 ... 9 mm            |
| Marking method              | Thermal transfer                         |
| Marking                     | plain                                    |
| Delivery form               | Roll                                     |
| Delivery form configuration | 1,000 pcs/reel                           |
| Printing device             | Smart Printer (thermal transfer printer) |

Physical data

|                 |           |
|-----------------|-----------|
| Depth           | 0.12 mm   |
| Marking surface | 9 x 18 mm |

Mechanical data

|                  |   |
|------------------|---|
| Mounting type    | Wrapping                                |
| Smear resistance | in conjunction with 258-5014 Ink Ribbon |

Material data

|                      |                               |
|----------------------|-------------------------------|
| Color                | white                         |
| Material             | Polyvinyl chloride            |
| UV resistance        | EN 60068-2-5:2010 Procedure B |
| Adhesive information | Acrylic; permanent            |
| Halogen-free         | Yes                           |
| Weight               | 129.6 g                       |
| Fire load            | 0 MJ                          |



| Environmental requirements      |                 |
|---------------------------------|-----------------|
| Ambient temperature (storage)   | +10 ... +22 °C  |
| Ambient temperature (operation) | -30 ... +120 °C |
| Relative humidity               | 40 ... 50 %     |

| Commercial data       |                                |
|-----------------------|--------------------------------|
| Product Group         | 2 (Terminal Block Accessories) |
| PU (SPU)              | 1 pcs                          |
| Packaging type        | Box                            |
| Country of origin     | DE                             |
| GTIN                  | 4050821656852                  |
| Customs tariff number | 39191080888                    |

| Product classification |                      |
|------------------------|----------------------|
| UNSPSC                 | 55121612             |
| eCl@ss 10.0            | 27-40-04-01          |
| eCl@ss 9.0             | 27-40-06-29          |
| ETIM 9.0               | EC001530             |
| ETIM 8.0               | EC001530             |
| ECCN                   | NO US CLASSIFICATION |

| Environmental Product Compliance |                         |
|----------------------------------|-------------------------|
| RoHS Compliance Status           | Compliant, No Exemption |

Downloads

Environmental Product Compliance

|  |  |
|--|--|
| Compliance Search                        |  |
| Environmental Product Compliance 211-855 |  |

Documentation

|  |            |            |  |
|--|------------|------------|--|
| Operating Instructions                   |            |            |  |
| 211-856 Information on printing material | 1          | pdf        |  |
|  | 28.08.2020 | 1316.17 KB |  |

Installation Notes

Marking



- Remove the printed label from the sheet or reel.
- Wrap the label around the conductor or cable.
- The transparent laminate protects the marking.

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](http://www.wago.com)