




**Part Number :** [2130281000](#)

**Product Description :** CLIK-Mate 1.50mm Pitch Crimp Terminal, Male, 0.10µm Gold Plating, 26-24 AWG, Reel

**Series Number :** 213028

**Status :** Active

**Product Category :** Crimp Terminals



---

## Documents and Resources

### Drawings

[2130281000\\_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[2130289200-SPK-200.pdf](#)

[5025781004-PS-000.pdf](#)

[5031491002-PS-000.pdf](#)


[5025780004-PS-000.pdf](#)

[5031490002-PS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

## Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	213028
Description	CLIK-Mate 1.50mm Pitch Crimp Terminal, Male, 0.10µm Gold Plating, 26-24 AWG, Reel
Application	Signal, Wire-to-Board
Product Name	CLIK-Mate
UPC	193264238569

### Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	100V AC (RMS)/DC

### Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold

Net Weight	22.967/mg
Packaging Type	Reel
Plating min - Mating	0.102µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.00-1.28mm
Wire Size (AWG)	24, 26
Wire Size mm <sup>2</sup>	N/A

## Mates With / Use With

### Use with Part(s)

Description	Part Number
1.50mm Pitch CLIK-Mate Dual Row Plug Housings	<u>503149</u>

---

## Application Tooling

### Global

Description	Part Number
Hand Crimp Tool for 1.50mm Pitch CLIK-Mate Wire-to-Board Crimp Terminals, 28-24 AWG	<u>2002187400</u>
Extractor Tool for 1.50mm Pitch Wire-to-Board Crimp Terminal	<u>638133700</u>
FineAdjust Applicator for 1.50mm Pitch Wire-to-Board Crimp Terminals	<u>639025000</u>

### Japan

Description	Part Number
S-1 Applicator for CLIK-Mate Plug Terminals, 28-24 AWG	<u>5780473700</u>