Part Number : 347910080
Product Description : Mini50 Unsealed Receptacle, Single Row, Non-Bridged, 8 Circuits, Polarization Option A, Black
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

347910080_sd.pdf

PK-31301-538-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-34791-020-CH-001.pdf

AS-34791-020-001.pdf

AS-34791-020-CH-001.pdf

AS-34791-020-FR-001.pdf

PS-34791-020-001.pdf

347910020-TS-000.pdf

Part Details

General

Status	Active
Category	Connector Housings
Series	34791
Description	Mini50 Unsealed Receptacle, Single Row, Non-Bridged, 8 Circuits, Polarization Option A, Black
Application	Automotive, Wire-to-Board
Component Type	Receptacle

Downloaded from Arrow.com.

Product Name	Mini50
UPC	884982491472

Physical

Circuits (maximum)	8
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	1.300/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarization	A
Polarized to Mating Part	Yes
Sealed	Unsealed
Stackable	No
Temperature Range - Operating	-40° to +105°C
Terminal Size	0.5

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description
Mini50 Unsealed Vertical Headers
Mini50 Unsealed Right-Angle Headers
Mini50 Unsealed Single Row Right-Angle Headers
Mini50 Unsealed Single Row Inline Housings

Downloaded from Arrow.com.

Use with Part(s)

Description
CTX50 Unsealed Receptacle Terminals

This document was generated on Nov 11, 2026

Downloaded from Arrow.com.