
Part Number : 535170310
Product Description : 2.50mm Pitch Mini-Lock Wire-to-Board PCB Header, Vertical, 3 Circuits
Series Number : 53517
Status : Obsolete
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

535170310_sd.pdf

SPK-53517-001-001.pdf

Specifications

535179200-SPK-201.pdf

PS-51103-006-001.pdf

PS-51103-024-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Obsolete

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	PCB Headers and Receptacles
Series	53517
Description	2.50mm Pitch Mini-Lock Wire-to-Board PCB Header, Vertical, 3 Circuits
Application	Wire-to-Board
Comments	Improvement on the recommended potting height spec, Mates With Series 51163
Component Type	PCB Header
Product Name	Mini-Lock
UPC	800753466234

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
First Mate / Last Break	No
Flammability	94V-0

Obsolete

Downloaded from Arrow.com.

Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Resin	Nylon
Net Weight	1071.700/mg
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.50mm
Pitch - Mating Interface	2.50mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Through Hole

Obsolete

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Lock Single Row Receptacle Housings	51103

Downloaded from Arrow.com.