



Part Number : [466261405](#)
Product Description : KK Plus 250 Female Crimp Terminal, 28-26 AWG, Tin (Sn) Plating, Reel
Series Number : 46626
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings


[466261405_sd.pdf](#)
[PK-46626-001-001.pdf](#)
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[2079020001-AS-000.pdf](#)
[2079020001-PS-000.pdf](#)
[2079020001-PS-CH-000.pdf](#)
[2079020001-PS-ES-000.pdf](#)
[2079020001-PS-JP-000.pdf](#)
[2079020001-PS-SK-000.pdf](#)
[2079020000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS

Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	46626
Description	KK Plus 250 Female Crimp Terminal, 28-26 AWG, Tin (Sn) Plating, Reel
Application	Power, Wire-to-Board
Product Name	KK Plus
UPC	191130122141

Electrical

Current - Maximum per Contact	6.5A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Durability (mating cycles max)	25
Gender	Female
Material - Metal	Copper Alloy

Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.043/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.17-1.30mm
Wire Size (AWG)	26, 28
Wire Size mm ²	0.08-0.13

Mates With / Use With

Use with Part(s)

Description	Part Number
KK Plus 250 Single Row Receptacle Housings	<u>207841</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for KK Plus 250 Receptacle Crimp Terminals, 28-22 AWG	<u>2002221000</u>
Hand Crimp Tool for KK Plus 250 Female Crimp Terminals, 28-22 AWG, UL1007 Wire	<u>2133090300</u>
Hand Crimp Tool for KK Plus 250 Female Crimp Terminals, 28-26 AWG, UL1061 Wire	<u>2133092200</u>
FineAdjust Applicator for KK Plus 250 Female Crimp Terminal, 28-26 AWG, UL1007 Wire	<u>639047500</u>

This document was generated on Apr 30, 2026