Product Details for 1-211992-1

No Image Available

1-211992-1

Active

ARINC 600 Connectors

Not ELV or RoHS Compliant

Product Highlights:

- Not Sealed
- Shell Size = 3
- Shell Configuration = Receptacle
- Contact Arrangement (Module A) = 150
- Contact Arrangement (Module B) = 150

View all Features

Quick Links

Check Pricing & Availability
Search for Tooling
Product Feature Selector
Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- CONNECTOR ASSY,SIZE 3 CLASS A, RCPT,ARINC-600 FRONT ... (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

List all Documents

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- Sealed = No
- Shell Size = 3
- Shell Finish = Chromate Conversion Coating
- Comment = Contacts must be ordered separately.; Front release/remove size 22 contacts; all other contact sizes rear release/remove.

Mechanical Attachment:

- Keying = 00
- Clinch Nut Size = 6-32

Electrical Characteristics:

- Shell Configuration = Receptacle
- Clinch Nuts = With

Body Related Features:

- Release Style = Front

Contact Related Features:

- Contacts = Without

Configuration Related Features:

- Contact Arrangement (Module A) = 150
- Contact Arrangement (Module B) = 150
- Contact Arrangement (Module C) = 13C2
- Contact Arrangement (Module D) = 150
- Contact Arrangement (Module E) = 150
- Contact Arrangement (Module F) = 13C2

Industry Standards:

- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

Purchasing Information:

- Clinch Nut Quantity = 10

Other:

- Brand = AMP

© 2006 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.